

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257750

Luminaire Tested: P3AS17R309040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 719.0 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257750
CATALOG NUMBER: P3AS17R309040DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1257750
 CATALOG NUMBER: P3AS17R309040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	91	89	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	88	85	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	78	75	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	76	72	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419550
5°	399339
10°	335888
15°	242226
20°	150256
25°	85457
30°	47476
35°	25806
40°	13597
45°	7381
50°	3923
55°	2600
60°	2368
65°	2491
70°	2180
75°	1694
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7381 cd/sqm



TEST NUMBER: P1257750
 CATALOG NUMBER: P3AS17R309040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.4	22.7
10°-20°	290.4	40.4
20°-30°	167.8	23.3
30°-40°	63.7	8.9
40°-50°	19.5	2.7
50°-60°	6.6	0.9
60°-70°	4.5	0.6
70°-80°	2.4	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	621.6	86.4
0°-40°	685.2	95.3
0°-60°	711.4	98.9
0°-90°	719.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	719.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1913	
5°	1814	163
15°	1067	290
25°	353	168
35°	96	64
45°	24	20
55°	7	7
65°	5	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1257750
CATALOG NUMBER: P3AS17R309040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1913.3
1°	1912.0
2°	1900.4
3°	1878.7
4°	1851.5
5°	1814.2
6°	1766.6
7°	1713.7
8°	1654.6
9°	1583.9
10°	1508.5
11°	1427.0
12°	1340.8
13°	1250.4
14°	1158.7
15°	1067.0
17.5°	841.5
20°	643.9
22.5°	477.5
25°	353.2
27.5°	256.7
30°	187.5
32.5°	135.2
35°	96.4
37.5°	67.2
40°	47.5
42.5°	33.3
45°	23.8
47.5°	16.3
50°	11.5
52.5°	8.2
55°	6.8
57.5°	6.1
60°	5.4
62.5°	4.8
65°	4.8
67.5°	4.1
70°	3.4
72.5°	2.7
75°	2.0
77.5°	2.0
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.0



TEST NUMBER: P1257750
CATALOG NUMBER: P3AS17R309040DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)