

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257126

Luminaire Tested: P3AS09R559040DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559040DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 858.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257126

CATALOG NUMBER: P3AS09R559040DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257126

CATALOG NUMBER: P3AS09R559040DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	235595
5°	233215
10°	225224
15°	208174
20°	179636
25°	141879
30°	100648
35°	64889
40°	38987
45°	21956
50°	11803
55°	4205
60°	3815
65°	3684
70°	3526
75°	3304
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21956 cd/sqm

TEST NUMBER: P1257126

CATALOG NUMBER: P3AS09R559040DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	11.6
10°-20°	253.6	29.6
20°-30°	265.7	31.0
30°-40°	155.0	18.1
40°-50°	58.0	6.8
50°-60°	13.6	1.6
60°-70°	7.0	0.8
70°-80°	4.1	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.0	72.1
0°-40°	774.0	90.2
0°-60°	845.7	98.6
0°-90°	858.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	858.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1074	
5°	1060	100
15°	917	254
25°	586	266
35°	242	155
45°	71	58
55°	11	14
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1257126

CATALOG NUMBER: P3AS09R559040DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1074.4
2.5°	1071.3
5°	1059.5
7.5°	1040.6
10°	1011.5
12.5°	970.5
15°	917.0
17.5°	849.3
20°	769.8
22.5°	680.9
25°	586.4
27.5°	489.6
30°	397.5
32.5°	314.1
35°	242.4
37.5°	184.2
40°	136.2
42.5°	97.6
45°	70.8
47.5°	51.2
50°	34.6
52.5°	19.7
55°	11.0
57.5°	9.4
60°	8.7
62.5°	7.9
65°	7.1
67.5°	6.3
70°	5.5
72.5°	4.7
75°	3.9
77.5°	3.1
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)