

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257135

Luminaire Tested: P3AS09R609040DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609040DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 943.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257135
CATALOG NUMBER: P3AS09R609040DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1257135

CATALOG NUMBER: P3AS09R609040DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.0	10.6
10°-20°	272.4	28.9
20°-30°	341.2	36.2
30°-40°	190.7	20.2
40°-50°	36.2	3.8
50°-60°	1.9	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	713.6	75.7
0°-40°	904.3	95.9
0°-60°	942.4	99.9
0°-90°	943.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	943.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1127	
5°	1060	100
15°	978	272
25°	763	341
35°	304	191
45°	42	36
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1257135

CATALOG NUMBER: P3AS09R609040DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1126.8
1°	1122.1
2°	1107.5
3°	1090.1
4°	1073.9
5°	1059.7
6°	1048.9
7°	1039.6
8°	1032.6
9°	1026.1
10°	1020.3
11°	1014.5
12°	1008.0
13°	999.9
14°	990.2
15°	977.9
16°	962.8
17°	945.9
18°	926.6
19°	904.6
20°	884.5
21°	862.9
22°	840.5
23°	817.0
24°	791.2
25°	762.6
26°	729.1
27°	691.6
28°	649.6
29°	604.9
30°	556.6
31°	508.0
32°	457.9
32.5°	430.5
33°	405.8
34°	354.5
35°	304.0
36°	258.5
37°	210.2
37.5°	188.2
38°	166.6
39°	134.2
40°	110.3
42.5°	67.1
45°	42.4



TEST NUMBER: P1257135
CATALOG NUMBER: P3AS09R609040DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	23.5
50°	8.5
52.5°	1.9
55°	1.2
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)