

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257137

Luminaire Tested: P3AS09R609040DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609040DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 943.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257137

CATALOG NUMBER: P3AS09R609040DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257137

CATALOG NUMBER: P3AS09R609040DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	247085
5°	233259
10°	227184
15°	221999
20°	206401
25°	184511
30°	140933
35°	81378
40°	31573
45°	13149
50°	2900
55°	459
60°	351
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13149 cd/sqm

TEST NUMBER: P1257137

CATALOG NUMBER: P3AS09R609040DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.0	10.6
10°-20°	272.4	28.9
20°-30°	341.2	36.2
30°-40°	190.7	20.2
40°-50°	36.2	3.8
50°-60°	1.9	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	713.6	75.7
0°-40°	904.3	95.9
0°-60°	942.4	99.9
0°-90°	943.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	943.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1127	
5°	1060	100
15°	978	272
25°	763	341
35°	304	191
45°	42	36
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1257137

CATALOG NUMBER: P3AS09R609040DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1126.8
1°	1122.1
2°	1107.5
3°	1090.1
4°	1073.9
5°	1059.7
6°	1048.9
7°	1039.6
8°	1032.6
9°	1026.1
10°	1020.3
11°	1014.5
12°	1008.0
13°	999.9
14°	990.2
15°	977.9
16°	962.8
17°	945.9
18°	926.6
19°	904.6
20°	884.5
21°	862.9
22°	840.5
23°	817.0
24°	791.2
25°	762.6
26°	729.1
27°	691.6
28°	649.6
29°	604.9
30°	556.6
31°	508.0
32°	457.9
32.5°	430.5
33°	405.8
34°	354.5
35°	304.0
36°	258.5
37°	210.2
37.5°	188.2
38°	166.6
39°	134.2
40°	110.3
42.5°	67.1
45°	42.4



TEST NUMBER: P1257137

CATALOG NUMBER: P3AS09R609040DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	23.5
50°	8.5
52.5°	1.9
55°	1.2
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)