

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257203

Luminaire Tested: P3AS09R709040DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257203  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709040DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 277.1 lumens  
Efficiency: N/A  
Efficacy: 25.0 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257203  
CATALOG NUMBER: P3AS09R709040DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1257203  
 CATALOG NUMBER: P3AS09R709040DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	64973
5°	63790
10°	60141
15°	54575
20°	47744
25°	40285
30°	32967
35°	25591
40°	18320
45°	11598
50°	5799
55°	3517
60°	3026
65°	2802
70°	2500
75°	2288
80°	1894
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11598 cd/sqm



TEST NUMBER: P1257203  
 CATALOG NUMBER: P3AS09R709040DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.0	9.8
10°-20°	66.9	24.1
20°-30°	76.2	27.5
30°-40°	59.6	21.5
40°-50°	29.3	10.6
50°-60°	9.0	3.2
60°-70°	5.3	1.9
70°-80°	2.8	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	170.1	61.4
0°-40°	229.7	82.9
0°-60°	268.0	96.7
0°-90°	277.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	296	
5°	290	27
15°	240	67
25°	166	76
35°	96	60
45°	37	29
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1257203  
CATALOG NUMBER: P3AS09R709040DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	296.3
2.5°	294.8
5°	289.8
7.5°	281.7
10°	270.1
12.5°	256.6
15°	240.4
17.5°	223.1
20°	204.6
22.5°	185.3
25°	166.5
27.5°	148.0
30°	130.2
32.5°	112.5
35°	95.6
37.5°	79.4
40°	64.0
42.5°	49.7
45°	37.4
47.5°	26.2
50°	17.0
52.5°	11.2
55°	9.2
57.5°	8.1
60°	6.9
62.5°	6.2
65°	5.4
67.5°	4.6
70°	3.9
72.5°	3.1
75°	2.7
77.5°	2.3
80°	1.5
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)