

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257876

Luminaire Tested: P3AS17R509040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 501.0 lumens
Efficiency: N/A
Efficacy: 23.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257876

CATALOG NUMBER: P3AS17R509040DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257876

CATALOG NUMBER: P3AS17R509040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145712
5°	141800
10°	130748
15°	114984
20°	96212
25°	76287
30°	55983
35°	38494
40°	24446
45°	13676
50°	7403
55°	6232
60°	5350
65°	4929
70°	4360
75°	3982
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13676 cd/sqm

TEST NUMBER: P1257876

CATALOG NUMBER: P3AS17R509040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.7	11.9
10°-20°	140.3	28.0
20°-30°	143.5	28.6
30°-40°	91.0	18.2
40°-50°	36.2	7.2
50°-60°	14.7	2.9
60°-70°	9.4	1.9
70°-80°	4.8	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.5	68.6
0°-40°	434.5	86.7
0°-60°	485.3	96.9
0°-90°	501.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	501.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	664	
5°	644	60
15°	506	140
25°	315	143
35°	144	91
45°	44	36
55°	16	15
65°	10	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1257876

CATALOG NUMBER: P3AS17R509040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	664.5
2.5°	659.8
5°	644.2
7.5°	619.8
10°	587.2
12.5°	548.6
15°	506.5
17.5°	460.4
20°	412.3
22.5°	364.1
25°	315.3
27.5°	266.5
30°	221.1
32.5°	180.4
35°	143.8
37.5°	112.6
40°	85.4
42.5°	63.1
45°	44.1
47.5°	29.8
50°	21.7
52.5°	18.3
55°	16.3
57.5°	14.2
60°	12.2
62.5°	10.8
65°	9.5
67.5°	8.1
70°	6.8
72.5°	5.4
75°	4.7
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)