

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257230

Luminaire Tested: P3AS10R129040DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS10R129040DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 762.0 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257230

CATALOG NUMBER: P3AS10R129040DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257230

CATALOG NUMBER: P3AS10R129040DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	650957
5°	577811
10°	401262
15°	237300
20°	135158
25°	77254
30°	42741
35°	22807
40°	12595
45°	6822
50°	4264
55°	3364
60°	2895
65°	2646
70°	2372
75°	2457
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6822 cd/sqm

TEST NUMBER: P1257230

CATALOG NUMBER: P3AS10R129040DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.2	29.3
10°-20°	294.6	38.7
20°-30°	151.7	19.9
30°-40°	57.0	7.5
40°-50°	18.6	2.4
50°-60°	8.0	1.1
60°-70°	5.1	0.7
70°-80°	3.0	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.5	87.9
0°-40°	726.5	95.3
0°-60°	753.1	98.8
0°-90°	762.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	762.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2969	
5°	2625	223
15°	1045	295
25°	319	152
35°	85	57
45°	22	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1257230

CATALOG NUMBER: P3AS10R129040DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2968.6
1°	2962.7
2°	2923.8
3°	2849.6
4°	2752.0
5°	2625.0
6°	2481.1
7°	2323.3
8°	2147.9
9°	1974.6
10°	1802.1
12.5°	1386.6
15°	1045.3
17.5°	782.5
20°	579.2
22.5°	432.4
25°	319.3
27.5°	232.7
30°	168.8
32.5°	119.7
35°	85.2
37.5°	60.9
40°	44.0
42.5°	31.6
45°	22.0
47.5°	16.1
50°	12.5
52.5°	10.3
55°	8.8
57.5°	7.3
60°	6.6
62.5°	5.9
65°	5.1
67.5°	4.4
70°	3.7
72.5°	3.7
75°	2.9
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)