

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257877

Luminaire Tested: P3AS17R509040DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257877  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R509040DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1023.0 lumens  
Efficiency: N/A  
Efficacy: 48.3 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257877  
CATALOG NUMBER: P3AS17R509040DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1257877  
 CATALOG NUMBER: P3AS17R509040DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68			
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	297542
5°	289522
10°	266973
15°	234803
20°	196437
25°	155767
30°	114296
35°	78568
40°	49951
45°	27910
50°	15113
55°	12692
60°	10920
65°	10066
70°	8848
75°	8218
80°	6945
85°	7045

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27910 cd/sqm



TEST NUMBER: P1257877  
 CATALOG NUMBER: P3AS17R509040DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.9	11.9
10°-20°	286.4	28.0
20°-30°	293.0	28.6
30°-40°	185.8	18.2
40°-50°	73.9	7.2
50°-60°	30.0	2.9
60°-70°	19.2	1.9
70°-80°	9.8	1.0
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.3	68.6
0°-40°	887.1	86.7
0°-60°	991.0	96.9
0°-90°	1023.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1023.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1357	
5°	1315	122
15°	1034	286
25°	644	293
35°	294	186
45°	90	74
55°	33	30
65°	19	19
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P1257877  
CATALOG NUMBER: P3AS17R509040DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1356.9
2.5°	1347.2
5°	1315.3
7.5°	1265.5
10°	1199.0
12.5°	1120.1
15°	1034.3
17.5°	940.1
20°	841.8
22.5°	743.5
25°	643.8
27.5°	544.1
30°	451.4
32.5°	368.3
35°	293.5
37.5°	229.8
40°	174.5
42.5°	128.8
45°	90.0
47.5°	60.9
50°	44.3
52.5°	37.4
55°	33.2
57.5°	29.1
60°	24.9
62.5°	22.2
65°	19.4
67.5°	16.6
70°	13.8
72.5°	11.1
75°	9.7
77.5°	6.9
80°	5.5
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)