

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257892

Luminaire Tested: P3AS17R559040DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559040DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1787.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257892
CATALOG NUMBER: P3AS17R559040DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1257892
 CATALOG NUMBER: P3AS17R559040DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	12.3
10°-20°	626.0	35.0
20°-30°	695.9	38.9
30°-40°	216.6	12.1
40°-50°	26.0	1.5
50°-60°	2.0	0.1
60°-70°	0.7	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1541.6	86.3
0°-40°	1758.2	98.4
0°-60°	1786.2	100.0
0°-90°	1787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1787.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2363	
5°	2271	220
15°	2248	626
25°	1579	696
35°	290	217
45°	31	26
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1257892
CATALOG NUMBER: P3AS17R559040DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2363.2
1°	2354.4
2°	2331.3
3°	2302.8
4°	2277.0
5°	2270.9
6°	2277.7
7°	2291.9
8°	2308.2
9°	2321.1
10°	2325.2
11°	2322.5
12°	2311.6
13°	2294.7
14°	2275.0
15°	2248.5
16°	2217.9
17°	2179.2
18°	2135.8
19°	2083.5
20°	2024.5
21°	1957.2
22°	1877.8
23°	1790.2
24°	1689.8
25°	1579.1
26°	1457.6
27°	1328.6
28°	1190.8
29°	1048.9
30°	904.3
31°	759.0
32°	617.1
32.5°	554.0
33°	488.8
34°	378.1
35°	289.9
36°	220.6
37°	163.6
37.5°	139.9
38°	121.5
39°	92.3
40°	74.7
42.5°	47.5
45°	30.6



TEST NUMBER: P1257892
CATALOG NUMBER: P3AS17R559040DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	18.3
50°	8.1
52.5°	2.7
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)