

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257274

Luminaire Tested: P3AS13R159040DE010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R159040DE010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1322.0 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257274  
CATALOG NUMBER: P3AS13R159040DE010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1257274  
 CATALOG NUMBER: P3AS13R159040DE010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94	94	94	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91	91	91	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89	89	89	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88	88	88	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86	86	86	86
9	97	92	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85	85	85	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84	84	84	84

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2569663
5°	2153615
10°	1014432
15°	305836
20°	113177
25°	44011
30°	16408
35°	5033
40°	1803
45°	961
50°	716
55°	803
60°	921
65°	519
70°	641
75°	847
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 961 cd/sqm



TEST NUMBER: P1257274  
 CATALOG NUMBER: P3AS13R159040DE010 E3CB1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	756.4	57.2
10°-20°	449.6	34.0
20°-30°	94.4	7.1
30°-40°	15.2	1.2
40°-50°	2.6	0.2
50°-60°	1.9	0.1
60°-70°	1.1	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1300.5	98.4
0°-40°	1315.7	99.5
0°-60°	1320.2	99.9
0°-90°	1322.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1322.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11719	
5°	9784	756
15°	1347	450
25°	182	94
35°	19	15
45°	3	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1257274  
CATALOG NUMBER: P3AS13R159040DE010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11718.6
1°	11682.0
2°	11495.9
3°	11123.8
4°	10578.3
5°	9783.9
6°	8850.6
7°	7783.5
8°	6764.4
9°	5610.5
10°	4555.9
12.5°	2458.3
15°	1347.2
17.5°	789.1
20°	485.0
22.5°	296.8
25°	181.9
27.5°	109.7
30°	64.8
32.5°	36.6
35°	18.8
37.5°	10.5
40°	6.3
42.5°	4.2
45°	3.1
47.5°	2.1
50°	2.1
52.5°	2.1
55°	2.1
57.5°	2.1
60°	2.1
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)