

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257290

Luminaire Tested: P3AS13R159040DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257290  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R159040DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 404.0 lumens  
Efficiency: N/A  
Efficacy: 27.7 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257290  
CATALOG NUMBER: P3AS13R159040DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1257290  
 CATALOG NUMBER: P3AS13R159040DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	101900
5°	99141
10°	90602
15°	79365
20°	68069
25°	56834
30°	45475
35°	34104
40°	24761
45°	16188
50°	10132
55°	6843
60°	6052
65°	5552
70°	5257
75°	4745
80°	4546
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16188 cd/sqm



TEST NUMBER: P1257290  
 CATALOG NUMBER: P3AS13R159040DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.6	10.3
10°-20°	97.4	24.1
20°-30°	107.3	26.6
30°-40°	80.3	19.9
40°-50°	41.7	10.3
50°-60°	17.3	4.3
60°-70°	10.7	2.6
70°-80°	6.0	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.3	61.0
0°-40°	326.6	80.8
0°-60°	385.5	95.4
0°-90°	404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	465	
5°	450	42
15°	350	97
25°	235	107
35°	127	80
45°	52	42
55°	18	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1257290  
CATALOG NUMBER: P3AS13R159040DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	464.7
1°	465.2
2°	463.7
3°	460.6
4°	456.0
5°	450.4
6°	443.2
7°	435.5
8°	426.3
9°	416.6
10°	406.9
12.5°	378.7
15°	349.6
17.5°	320.4
20°	291.7
22.5°	262.6
25°	234.9
27.5°	207.3
30°	179.6
32.5°	152.5
35°	127.4
37.5°	105.9
40°	86.5
42.5°	68.6
45°	52.2
47.5°	39.4
50°	29.7
52.5°	22.0
55°	17.9
57.5°	15.9
60°	13.8
62.5°	12.3
65°	10.7
67.5°	9.2
70°	8.2
72.5°	6.7
75°	5.6
77.5°	4.6
80°	3.6
82.5°	2.6
85°	1.5
87.5°	0.5
90°	0.0

(END OF REPORT)