

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257915

Luminaire Tested: P3AS17R609040DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609040DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1791.1 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257915

CATALOG NUMBER: P3AS17R609040DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1257915

CATALOG NUMBER: P3AS17R609040DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	427685
5°	410719
10°	422860
15°	428311
20°	378196
25°	318720
30°	258495
35°	168352
40°	77316
45°	29646
50°	9927
55°	2638
60°	2412
65°	2179
70°	1795
75°	2372
80°	1768
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29646 cd/sqm

TEST NUMBER: P1257915

CATALOG NUMBER: P3AS17R609040DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.6	10.0
10°-20°	516.7	28.8
20°-30°	602.6	33.6
30°-40°	388.9	21.7
40°-50°	87.1	4.9
50°-60°	8.7	0.5
60°-70°	4.1	0.2
70°-80°	2.4	0.1
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.9	72.5
0°-40°	1687.7	94.2
0°-60°	1783.6	99.6
0°-90°	1791.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1791.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1950	
5°	1866	180
15°	1887	517
25°	1317	603
35°	629	389
45°	96	87
55°	7	9
65°	4	4
75°	3	2
85°	1	1
90°	0	

TEST NUMBER: P1257915

CATALOG NUMBER: P3AS17R609040DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1950.4
2.5°	1918.5
5°	1865.9
7.5°	1863.1
10°	1899.1
12.5°	1922.7
15°	1886.7
17.5°	1778.6
20°	1620.7
22.5°	1455.9
25°	1317.3
27.5°	1181.6
30°	1020.9
32.5°	832.5
35°	628.9
37.5°	429.4
40°	270.1
42.5°	162.1
45°	95.6
47.5°	55.4
50°	29.1
52.5°	9.7
55°	6.9
57.5°	5.5
60°	5.5
62.5°	4.2
65°	4.2
67.5°	4.2
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)