

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257981

Luminaire Tested: P3AS17R709040DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709040DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1395.1 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257981

CATALOG NUMBER: P3AS17R709040DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1257981

CATALOG NUMBER: P3AS17R709040DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	92	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	82		89	85	81		86	83	80		84	81	79
4	94	86	80	75		93	85	79	75		83	78	74		81	76	73		79	75	72
5	89	80	73	69		87	79	73	68		77	72	68		75	71	67		74	70	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	53		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	50	46		66	56	50	46		55	50	46		55	49	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270066
5°	266827
10°	259113
15°	248129
20°	232444
25°	211173
30°	182408
35°	145384
40°	105884
45°	69589
50°	32613
55°	10055
60°	9736
65°	9340
70°	8912
75°	9404
80°	8713
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 69589 cd/sqm

TEST NUMBER: P1257981

CATALOG NUMBER: P3AS17R709040DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.1	8.2
10°-20°	305.9	21.9
20°-30°	397.6	28.5
30°-40°	337.4	24.2
40°-50°	174.0	12.5
50°-60°	33.5	2.4
60°-70°	18.2	1.3
70°-80°	11.2	0.8
80°-90°	3.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.6	58.6
0°-40°	1155.0	82.8
0°-60°	1362.5	97.7
0°-90°	1395.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1395.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1232	
5°	1212	114
15°	1093	306
25°	873	398
35°	543	337
45°	224	174
55°	26	34
65°	18	18
75°	11	11
85°	3	3
90°	0	

TEST NUMBER: P1257981

CATALOG NUMBER: P3AS17R709040DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1231.6
2.5°	1227.4
5°	1212.2
7.5°	1190.0
10°	1163.7
12.5°	1130.4
15°	1093.0
17.5°	1047.3
20°	996.1
22.5°	937.9
25°	872.8
27.5°	799.3
30°	720.4
32.5°	633.1
35°	543.1
37.5°	454.4
40°	369.9
42.5°	290.9
45°	224.4
47.5°	164.9
50°	95.6
52.5°	41.6
55°	26.3
57.5°	24.9
60°	22.2
62.5°	20.8
65°	18.0
67.5°	16.6
70°	13.9
72.5°	12.5
75°	11.1
77.5°	8.3
80°	6.9
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)