

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257372

Luminaire Tested: P3AS13R309040DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309040DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1320.0 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257372

CATALOG NUMBER: P3AS13R309040DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257372

CATALOG NUMBER: P3AS13R309040DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		113	111	109	108		107	106	104		103	102	101		100	99	98
2	111	108	105	102		109	106	103	101		103	101	99		100	98	97		97	96	95
3	108	103	100	97		106	102	99	96		99	97	95		97	95	93		95	93	92
4	105	99	95	92		103	98	95	92		96	93	91		94	92	90		93	91	89
5	101	96	92	89		100	95	91	88		93	90	87		92	89	87		90	88	86
6	99	92	88	85		97	92	88	85		90	87	85		89	86	84		88	85	83
7	96	89	85	82		95	89	85	82		88	84	82		87	84	81		86	83	81
8	93	87	83	80		92	86	82	80		85	82	79		84	81	79		84	81	79
9	91	84	80	77		90	84	80	77		83	79	77		82	79	77		82	79	77
10	88	82	78	75		88	81	78	75		81	77	75		80	77	75		80	77	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1050223
5°	1036537
10°	904993
15°	575213
20°	227893
25°	76117
30°	35423
35°	16062
40°	6154
45°	3008
50°	887
55°	382
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3008 cd/sqm

TEST NUMBER: P1257372

CATALOG NUMBER: P3AS13R309040DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.5	32.6
10°-20°	667.6	50.6
20°-30°	172.2	13.0
30°-40°	40.4	3.1
40°-50°	7.9	0.6
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1270.3	96.2
0°-40°	1310.8	99.3
0°-60°	1319.5	100.0
0°-90°	1320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4789	
5°	4709	431
15°	2534	668
25°	315	172
35°	60	40
45°	10	8
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1257372

CATALOG NUMBER: P3AS13R309040DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4789.4
1°	4785.9
2°	4774.6
3°	4761.8
4°	4742.8
5°	4709.0
6°	4654.2
7°	4563.0
8°	4438.4
9°	4276.0
10°	4064.4
11°	3812.8
12°	3538.2
13°	3222.0
14°	2891.0
15°	2533.8
16°	2183.9
17°	1846.7
18°	1523.4
19°	1226.7
20°	976.6
21°	768.6
22°	604.6
23°	478.6
24°	383.3
25°	314.6
26°	262.4
27°	222.9
28°	192.7
29°	165.0
30°	139.9
32.5°	88.1
35°	60.0
37.5°	37.4
40°	21.5
42.5°	14.3
45°	9.7
47.5°	5.6
50°	2.6
52.5°	1.0
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P1257372

CATALOG NUMBER: P3AS13R309040DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)