

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257386

Luminaire Tested: P3AS13R309040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 330.0 lumens
Efficiency: N/A
Efficacy: 22.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257386

CATALOG NUMBER: P3AS13R309040DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257386

CATALOG NUMBER: P3AS13R309040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112776
5°	109267
10°	98440
15°	81431
20°	63052
25°	47301
30°	34334
35°	22888
40°	14055
45°	8249
50°	5049
55°	4091
60°	3596
65°	2906
70°	2629
75°	2626
80°	1894
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8249 cd/sqm

TEST NUMBER: P1257386

CATALOG NUMBER: P3AS13R309040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	13.8
10°-20°	98.8	29.9
20°-30°	89.9	27.2
30°-40°	54.3	16.5
40°-50°	21.8	6.6
50°-60°	9.6	2.9
60°-70°	5.8	1.8
70°-80°	3.2	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.3	71.0
0°-40°	288.7	87.5
0°-60°	320.1	97.0
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	514	
5°	496	46
15°	359	99
25°	196	90
35°	86	54
45°	27	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1257386

CATALOG NUMBER: P3AS13R309040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	514.3
1°	513.7
2°	511.7
3°	508.1
4°	503.0
5°	496.4
6°	488.2
7°	479.5
8°	468.2
9°	455.4
10°	442.1
11°	426.8
12°	410.4
13°	394.0
14°	376.1
15°	358.7
17.5°	313.2
20°	270.2
22.5°	230.3
25°	195.5
27.5°	163.7
30°	135.6
32.5°	109.5
35°	85.5
37.5°	65.5
40°	49.1
42.5°	35.8
45°	26.6
47.5°	20.0
50°	14.8
52.5°	11.8
55°	10.7
57.5°	9.2
60°	8.2
62.5°	6.7
65°	5.6
67.5°	5.1
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.6
80°	1.5
82.5°	1.0
85°	1.0
87.5°	0.5



TEST NUMBER: P1257386

CATALOG NUMBER: P3AS13R309040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)