

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258035

Luminaire Tested: P3AS20R209040D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209040D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2280.0 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258035

CATALOG NUMBER: P3AS20R209040D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1258035

CATALOG NUMBER: P3AS20R209040D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	89	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	87	87	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	83	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	81	81	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3458583
5°	2911967
10°	1818782
15°	679981
20°	233400
25°	97264
30°	45830
35°	20532
40°	9704
45°	4962
50°	1808
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4962 cd/sqm

TEST NUMBER: P1258035

CATALOG NUMBER: P3AS20R209040D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1100.1	48.3
10°-20°	906.2	39.7
20°-30°	205.9	9.0
30°-40°	52.4	2.3
40°-50°	13.2	0.6
50°-60°	1.7	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2212.2	97.0
0°-40°	2264.6	99.3
0°-60°	2279.5	100.0
0°-90°	2280.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2280.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15772	
5°	13229	###
15°	2995	906
25°	402	206
35°	77	52
45°	16	13
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1258035

CATALOG NUMBER: P3AS20R209040D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	15772.4
1°	15638.7
2°	15244.6
3°	14679.5
4°	13985.9
5°	13229.1
6°	12385.8
7°	11455.1
8°	10369.3
9°	9293.3
10°	8168.3
11°	6971.1
12°	5775.7
13°	4763.0
14°	3794.9
15°	2995.3
16°	2364.1
17°	1864.9
18°	1498.5
19°	1218.6
20°	1000.2
21°	836.2
22°	698.0
23°	580.3
24°	484.1
25°	402.0
27.5°	263.0
30°	181.0
32.5°	111.4
35°	76.7
37.5°	49.0
40°	33.9
42.5°	23.2
45°	16.0
47.5°	10.7
50°	5.3
52.5°	2.7
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1258035

CATALOG NUMBER: P3AS20R209040D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)