

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257400

Luminaire Tested: P3AS13R359040DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359040DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1328.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257400

CATALOG NUMBER: P3AS13R359040DE010 E3CD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1257400

CATALOG NUMBER: P3AS13R359040DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97	95	94	93
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	865939
5°	848292
10°	789186
15°	578596
20°	296266
25°	106772
30°	41576
35°	14562
40°	5983
45°	1613
50°	1433
55°	1606
60°	1360
65°	1090
70°	1346
75°	1779
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 1779 cd/sqm

TEST NUMBER: P1257400

CATALOG NUMBER: P3AS13R359040DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.3	27.1
10°-20°	674.1	50.8
20°-30°	238.6	18.0
30°-40°	41.8	3.1
40°-50°	6.1	0.5
50°-60°	3.4	0.3
60°-70°	2.4	0.2
70°-80°	1.8	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1272.0	95.8
0°-40°	1313.8	98.9
0°-60°	1323.3	99.7
0°-90°	1328.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1328.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3949	
5°	3854	359
15°	2549	674
25°	441	239
35°	54	42
45°	5	6
55°	4	3
65°	2	2
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1257400

CATALOG NUMBER: P3AS13R359040DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3949.0
1°	3948.0
2°	3935.4
3°	3911.4
4°	3889.4
5°	3853.8
6°	3817.2
7°	3776.5
8°	3726.3
9°	3647.8
10°	3544.3
11°	3401.0
12°	3228.4
13°	3023.5
14°	2797.6
15°	2548.7
17.5°	1898.2
20°	1269.6
22.5°	765.5
25°	441.3
27.5°	263.5
30°	164.2
32.5°	95.2
35°	54.4
37.5°	34.5
40°	20.9
42.5°	10.5
45°	5.2
47.5°	4.2
50°	4.2
52.5°	4.2
55°	4.2
57.5°	3.1
60°	3.1
62.5°	3.1
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1257400

CATALOG NUMBER: P3AS13R359040DE010 E3CD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)