

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258085

Luminaire Tested: P3AS20R309040D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309040D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2313.9 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258085

CATALOG NUMBER: P3AS20R309040D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1258085

CATALOG NUMBER: P3AS20R309040D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85		90	87	85		89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76		81	78	76		80	77	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1884367
5°	1848774
10°	1636621
15°	1036896
20°	393598
25°	116547
30°	46032
35°	14107
40°	6240
45°	2264
50°	1876
55°	1376
60°	1579
65°	1868
70°	1154
75°	1525
80°	2273
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 2273 cd/sqm

TEST NUMBER: P1258085

CATALOG NUMBER: P3AS20R309040D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	772.1	33.4
10°-20°	1203.3	52.0
20°-30°	279.4	12.1
30°-40°	43.3	1.9
40°-50°	7.4	0.3
50°-60°	3.4	0.1
60°-70°	2.9	0.1
70°-80°	1.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2254.8	97.4
0°-40°	2298.1	99.3
0°-60°	2308.9	99.8
0°-90°	2313.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2313.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8593	
5°	8399	772
15°	4568	1203
25°	482	279
35°	53	43
45°	7	7
55°	4	3
65°	4	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1258085

CATALOG NUMBER: P3AS20R309040D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	8593.4
1°	8588.0
2°	8564.4
3°	8524.4
4°	8473.5
5°	8399.0
6°	8306.3
7°	8168.1
8°	7979.1
9°	7701.0
10°	7350.2
11°	6897.7
12°	6386.9
13°	5819.8
14°	5196.4
15°	4567.5
17.5°	2988.1
20°	1686.7
22.5°	861.5
25°	481.7
27.5°	296.3
30°	181.8
32.5°	98.1
35°	52.7
37.5°	34.5
40°	21.8
42.5°	12.7
45°	7.3
47.5°	5.5
50°	5.5
52.5°	3.6
55°	3.6
57.5°	3.6
60°	3.6
62.5°	3.6
65°	3.6
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1258085

CATALOG NUMBER: P3AS20R309040D010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)