

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258094

Luminaire Tested: P3AS20R309040D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258094
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309040D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2296.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258094

CATALOG NUMBER: P3AS20R309040D010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1258094

CATALOG NUMBER: P3AS20R309040D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97
3	108	103	100	97	106	102	99	96	99	97	95		97	95	93		95
4	105	99	95	92	103	98	95	92	96	93	91		94	92	90		93
5	101	96	92	89	100	95	91	88	93	90	87		92	89	87		90
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88
7	96	89	85	82	95	89	85	82	88	84	82		87	84	81		86
8	93	87	83	80	92	86	82	80	85	82	79		84	81	79		84
9	91	84	80	77	90	84	80	77	83	79	77		82	79	77		82
10	88	82	78	75	88	81	78	75	81	77	75		80	77	75		80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1826762
5°	1802945
10°	1574141
15°	1000528
20°	396421
25°	132395
30°	61604
35°	27920
40°	10706
45°	5241
50°	1535
55°	688
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5241 cd/sqm

TEST NUMBER: P1258094

CATALOG NUMBER: P3AS20R309040D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	748.9	32.6
10°-20°	1161.3	50.6
20°-30°	299.4	13.0
30°-40°	70.3	3.1
40°-50°	13.7	0.6
50°-60°	1.6	0.1
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2209.6	96.2
0°-40°	2279.9	99.3
0°-60°	2295.2	100.0
0°-90°	2296.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2296.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8331	
5°	8191	749
15°	4407	1161
25°	547	299
35°	104	70
45°	17	14
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1258094

CATALOG NUMBER: P3AS20R309040D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	8330.7
1°	8324.5
2°	8304.9
3°	8282.6
4°	8249.6
5°	8190.8
6°	8095.4
7°	7936.8
8°	7720.2
9°	7437.7
10°	7069.6
11°	6632.0
12°	6154.2
13°	5604.3
14°	5028.6
15°	4407.3
16°	3798.6
17°	3212.1
18°	2649.8
19°	2133.7
20°	1698.8
21°	1336.9
22°	1051.7
23°	832.4
24°	666.7
25°	547.2
26°	456.3
27°	387.7
28°	335.1
29°	287.0
30°	243.3
32.5°	153.3
35°	104.3
37.5°	65.1
40°	37.4
42.5°	25.0
45°	16.9
47.5°	9.8
50°	4.5
52.5°	1.8
55°	1.8
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9



TEST NUMBER: P1258094

CATALOG NUMBER: P3AS20R309040D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)