

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258130

Luminaire Tested: P3AS20R359040D010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258130  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R359040D010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1471.0 lumens  
Efficiency: N/A  
Efficacy: 51.1 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258130  
CATALOG NUMBER: P3AS20R359040D010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1258130  
 CATALOG NUMBER: P3AS20R359040D010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	336026
5°	328901
10°	308010
15°	276483
20°	240518
25°	204955
30°	171672
35°	136737
40°	98871
45°	62580
50°	34114
55°	23626
60°	22323
65°	20754
70°	19811
75°	16945
80°	16037
85°	13838

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 62580 cd/sqm



TEST NUMBER: P1258130  
 CATALOG NUMBER: P3AS20R359040D010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.1	9.5
10°-20°	338.9	23.0
20°-30°	388.4	26.4
30°-40°	316.9	21.5
40°-50°	159.8	10.9
50°-60°	59.4	4.0
60°-70°	39.8	2.7
70°-80°	22.0	1.5
80°-90°	6.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	866.4	58.9
0°-40°	1183.3	80.4
0°-60°	1402.5	95.3
0°-90°	1471.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1471.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1532	
5°	1494	139
15°	1218	339
25°	847	388
35°	511	317
45°	202	160
55°	62	59
65°	40	40
75°	20	22
85°	6	7
90°	0	



TEST NUMBER: P1258130  
CATALOG NUMBER: P3AS20R359040D010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1532.4
1°	1530.6
2°	1526.9
3°	1519.7
4°	1508.7
5°	1494.2
6°	1476.0
7°	1457.8
8°	1434.2
9°	1410.6
10°	1383.3
11°	1354.2
12°	1323.3
13°	1288.8
14°	1252.4
15°	1217.9
17.5°	1125.2
20°	1030.7
22.5°	934.3
25°	847.1
27.5°	761.6
30°	678.0
32.5°	594.4
35°	510.8
37.5°	427.2
40°	345.4
42.5°	269.0
45°	201.8
47.5°	145.4
50°	100.0
52.5°	72.7
55°	61.8
57.5°	56.4
60°	50.9
62.5°	45.4
65°	40.0
67.5°	34.5
70°	30.9
72.5°	25.4
75°	20.0
77.5°	16.4
80°	12.7
82.5°	9.1
85°	5.5
87.5°	3.6



TEST NUMBER: P1258130  
CATALOG NUMBER: P3AS20R359040D010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)