

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258139

Luminaire Tested: P3AS20R359040D010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359040D010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1911.0 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258139
CATALOG NUMBER: P3AS20R359040D010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1258139
 CATALOG NUMBER: P3AS20R359040D010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	963826
5°	926302
10°	807088
15°	618165
20°	413573
25°	250248
30°	143592
35°	80281
40°	42680
45°	21987
50°	10541
55°	8334
60°	7982
65°	6590
70°	6988
75°	6185
80°	6945
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21987 cd/sqm



TEST NUMBER: P1258139
 CATALOG NUMBER: P3AS20R359040D010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.9	20.0
10°-20°	742.0	38.8
20°-30°	485.7	25.4
30°-40°	197.1	10.3
40°-50°	59.1	3.1
50°-60°	20.1	1.1
60°-70°	13.5	0.7
70°-80°	7.9	0.4
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1610.6	84.3
0°-40°	1807.7	94.6
0°-60°	1886.9	98.7
0°-90°	1911.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1911.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4395	
5°	4208	383
15°	2723	742
25°	1034	486
35°	300	197
45°	71	59
55°	22	20
65°	13	13
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1258139
CATALOG NUMBER: P3AS20R359040D010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4395.4
1°	4388.1
2°	4368.1
3°	4328.1
4°	4280.9
5°	4208.2
6°	4117.3
7°	4015.5
8°	3901.0
9°	3770.1
10°	3624.7
11°	3462.9
12°	3293.8
13°	3104.8
14°	2924.8
15°	2723.0
17.5°	2234.1
20°	1772.3
22.5°	1363.3
25°	1034.3
27.5°	770.7
30°	567.1
32.5°	416.3
35°	299.9
37.5°	212.7
40°	149.1
42.5°	103.6
45°	70.9
47.5°	47.3
50°	30.9
52.5°	23.6
55°	21.8
57.5°	20.0
60°	18.2
62.5°	16.4
65°	12.7
67.5°	10.9
70°	10.9
72.5°	9.1
75°	7.3
77.5°	5.5
80°	5.5
82.5°	3.6
85°	1.8
87.5°	1.8



TEST NUMBER: P1258139
CATALOG NUMBER: P3AS20R359040D010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)