

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257546

Luminaire Tested: P3AS13R609040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 539.0 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257546

CATALOG NUMBER: P3AS13R609040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257546

CATALOG NUMBER: P3AS13R609040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127271
5°	126062
10°	122398
15°	114666
20°	101485
25°	84900
30°	66542
35°	48265
40°	32117
45°	20002
50°	10848
55°	3135
60°	2938
65°	2646
70°	2629
75°	2626
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20002 cd/sqm

TEST NUMBER: P1257546

CATALOG NUMBER: P3AS13R609040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	10.0
10°-20°	140.1	26.0
20°-30°	159.7	29.6
30°-40°	113.3	21.0
40°-50°	51.4	9.5
50°-60°	10.9	2.0
60°-70°	5.2	1.0
70°-80°	3.3	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.8	65.6
0°-40°	467.1	86.7
0°-60°	529.4	98.2
0°-90°	539.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	539.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	580	
5°	573	54
15°	505	140
25°	351	160
35°	180	113
45°	64	51
55°	8	11
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1257546

CATALOG NUMBER: P3AS13R609040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	580.4
2.5°	578.4
5°	572.7
7.5°	563.0
10°	549.7
12.5°	530.7
15°	505.1
17.5°	472.8
20°	434.9
22.5°	393.9
25°	350.9
27.5°	306.9
30°	262.8
32.5°	220.8
35°	180.3
37.5°	144.5
40°	112.2
42.5°	85.0
45°	64.5
47.5°	48.2
50°	31.8
52.5°	14.9
55°	8.2
57.5°	7.2
60°	6.7
62.5°	6.1
65°	5.1
67.5°	4.6
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.6
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)