

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257559

Luminaire Tested: P3AS13R609040DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257559  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R609040DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 760.0 lumens  
Efficiency: N/A  
Efficacy: 52.1 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257559  
CATALOG NUMBER: P3AS13R609040DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1257559  
 CATALOG NUMBER: P3AS13R609040DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	192616
5°	188289
10°	176283
15°	158139
20°	135998
25°	112458
30°	88849
35°	65986
40°	45457
45°	28499
50°	15692
55°	9175
60°	8245
65°	7057
70°	6027
75°	6185
80°	5304
85°	5284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28499 cd/sqm



TEST NUMBER: P1257559  
 CATALOG NUMBER: P3AS13R609040DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.6	10.5
10°-20°	193.5	25.5
20°-30°	212.2	27.9
30°-40°	154.6	20.3
40°-50°	73.0	9.6
50°-60°	23.9	3.1
60°-70°	13.6	1.8
70°-80°	7.3	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.3	63.9
0°-40°	639.9	84.2
0°-60°	736.9	97.0
0°-90°	760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	760.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	878	
5°	855	80
15°	697	193
25°	465	212
35°	246	155
45°	92	73
55°	24	24
65°	14	14
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1257559  
CATALOG NUMBER: P3AS13R609040DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	878.4
2.5°	873.1
5°	855.4
7.5°	828.2
10°	791.7
12.5°	747.8
15°	696.6
17.5°	641.3
20°	582.8
22.5°	523.3
25°	464.8
27.5°	406.3
30°	350.9
32.5°	297.7
35°	246.5
37.5°	200.5
40°	158.8
42.5°	122.2
45°	91.9
47.5°	66.8
50°	46.0
52.5°	30.3
55°	24.0
57.5°	20.9
60°	18.8
62.5°	15.7
65°	13.6
67.5°	11.5
70°	9.4
72.5°	8.4
75°	7.3
77.5°	5.2
80°	4.2
82.5°	3.1
85°	2.1
87.5°	1.0
90°	0.0

(END OF REPORT)