

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257560

Luminaire Tested: P3AS13R609040DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609040DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 760.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257560

CATALOG NUMBER: P3AS13R609040DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1257560

CATALOG NUMBER: P3AS13R609040DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192616
5°	188289
10°	176283
15°	158139
20°	135998
25°	112458
30°	88849
35°	65986
40°	45457
45°	28499
50°	15692
55°	9175
60°	8245
65°	7057
70°	6027
75°	6185
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28499 cd/sqm

TEST NUMBER: P1257560

CATALOG NUMBER: P3AS13R609040DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.6	10.5
10°-20°	193.5	25.5
20°-30°	212.2	27.9
30°-40°	154.6	20.3
40°-50°	73.0	9.6
50°-60°	23.9	3.1
60°-70°	13.6	1.8
70°-80°	7.3	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.3	63.9
0°-40°	639.9	84.2
0°-60°	736.9	97.0
0°-90°	760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	760.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	878	
5°	855	80
15°	697	193
25°	465	212
35°	246	155
45°	92	73
55°	24	24
65°	14	14
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1257560

CATALOG NUMBER: P3AS13R609040DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	878.4
2.5°	873.1
5°	855.4
7.5°	828.2
10°	791.7
12.5°	747.8
15°	696.6
17.5°	641.3
20°	582.8
22.5°	523.3
25°	464.8
27.5°	406.3
30°	350.9
32.5°	297.7
35°	246.5
37.5°	200.5
40°	158.8
42.5°	122.2
45°	91.9
47.5°	66.8
50°	46.0
52.5°	30.3
55°	24.0
57.5°	20.9
60°	18.8
62.5°	15.7
65°	13.6
67.5°	11.5
70°	9.4
72.5°	8.4
75°	7.3
77.5°	5.2
80°	4.2
82.5°	3.1
85°	2.1
87.5°	1.0
90°	0.0

(END OF REPORT)