

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257565

Luminaire Tested: P3AS13R659040DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659040DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1293.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257565

CATALOG NUMBER: P3AS13R659040DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1257565

CATALOG NUMBER: P3AS13R659040DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315983
5°	297402
10°	293604
15°	288424
20°	272324
25°	252765
30°	196461
35°	113662
40°	45800
45°	21087
50°	8221
55°	3211
60°	2763
65°	2698
70°	2693
75°	2626
80°	2652
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21087 cd/sqm

TEST NUMBER: P1257565

CATALOG NUMBER: P3AS13R659040DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	9.9
10°-20°	354.8	27.4
20°-30°	464.5	35.9
30°-40°	269.0	20.8
40°-50°	57.6	4.5
50°-60°	9.4	0.7
60°-70°	5.2	0.4
70°-80°	3.0	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	947.7	73.3
0°-40°	1216.7	94.1
0°-60°	1283.7	99.3
0°-90°	1293.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1293.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1441	
5°	1351	128
15°	1270	355
25°	1045	464
35°	425	269
45°	68	58
55°	8	9
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1257565

CATALOG NUMBER: P3AS13R659040DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1441.0
2.5°	1400.2
5°	1351.1
7.5°	1331.2
10°	1318.6
12.5°	1300.9
15°	1270.5
17.5°	1223.5
20°	1167.0
22.5°	1113.7
25°	1044.7
27.5°	928.6
30°	775.9
32.5°	601.3
35°	424.6
37.5°	268.7
40°	160.0
42.5°	100.4
45°	68.0
47.5°	43.9
50°	24.1
52.5°	11.5
55°	8.4
57.5°	7.3
60°	6.3
62.5°	6.3
65°	5.2
67.5°	4.2
70°	4.2
72.5°	3.1
75°	3.1
77.5°	2.1
80°	2.1
82.5°	1.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)