

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258201

Luminaire Tested: P3AS20R509040D010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509040D010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2489.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258201
CATALOG NUMBER: P3AS20R509040D010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1258201
 CATALOG NUMBER: P3AS20R509040D010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65	65	65	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	866838
5°	851330
10°	817420
15°	749584
20°	660974
25°	506618
30°	275460
35°	88633
40°	20839
45°	2822
50°	2490
55°	2791
60°	2412
65°	2854
70°	2308
75°	3050
80°	2273
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 4529 cd/sqm



TEST NUMBER: P1258201
 CATALOG NUMBER: P3AS20R509040D010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	362.9	14.6
10°-20°	917.8	36.9
20°-30°	919.2	36.9
30°-40°	258.5	10.4
40°-50°	15.6	0.6
50°-60°	5.9	0.2
60°-70°	4.7	0.2
70°-80°	3.1	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2200.0	88.4
0°-40°	2458.4	98.8
0°-60°	2480.0	99.6
0°-90°	2489.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2489.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3953	
5°	3868	363
15°	3302	918
25°	2094	919
35°	331	258
45°	9	16
55°	7	6
65°	6	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P1258201
CATALOG NUMBER: P3AS20R509040D010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3953.1
2.5°	3933.1
5°	3867.6
7.5°	3778.5
10°	3671.1
12.5°	3509.2
15°	3301.9
17.5°	3063.5
20°	2832.5
22.5°	2545.1
25°	2093.9
27.5°	1559.1
30°	1087.9
32.5°	656.7
35°	331.1
37.5°	156.5
40°	72.8
42.5°	27.3
45°	9.1
47.5°	7.3
50°	7.3
52.5°	7.3
55°	7.3
57.5°	5.5
60°	5.5
62.5°	5.5
65°	5.5
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)