

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257575

Luminaire Tested: P3AS13R659040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 514.0 lumens
Efficiency: N/A
Efficacy: 35.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257575

CATALOG NUMBER: P3AS13R659040DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1257575

CATALOG NUMBER: P3AS13R659040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121218
5°	119766
10°	115206
15°	107923
20°	97075
25°	82432
30°	64466
35°	45936
40°	30056
45°	18576
50°	9450
55°	3326
60°	2938
65°	2906
70°	2629
75°	2626
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 18576 cd/sqm

TEST NUMBER: P1257575

CATALOG NUMBER: P3AS13R659040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.1	9.9
10°-20°	132.3	25.7
20°-30°	154.6	30.1
30°-40°	108.1	21.0
40°-50°	47.6	9.3
50°-60°	10.6	2.1
60°-70°	5.4	1.0
70°-80°	3.3	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.0	65.8
0°-40°	446.1	86.8
0°-60°	504.3	98.1
0°-90°	514.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	514.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	553	
5°	544	51
15°	475	132
25°	341	155
35°	172	108
45°	60	48
55°	9	11
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1257575

CATALOG NUMBER: P3AS13R659040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	552.8
2.5°	550.7
5°	544.1
7.5°	532.8
10°	517.4
12.5°	498.5
15°	475.4
17.5°	447.3
20°	416.0
22.5°	380.7
25°	340.7
27.5°	298.7
30°	254.6
32.5°	212.1
35°	171.6
37.5°	136.3
40°	105.0
42.5°	79.4
45°	59.9
47.5°	44.1
50°	27.7
52.5°	14.3
55°	8.7
57.5°	7.7
60°	6.7
62.5°	6.1
65°	5.6
67.5°	4.6
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.6
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)