

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258205

Luminaire Tested: P3AS20R509040D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509040D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2525.0 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258205

CATALOG NUMBER: P3AS20R509040D010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1258205

CATALOG NUMBER: P3AS20R509040D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	882385
5°	858902
10°	819624
15°	742025
20°	641956
25°	526579
30°	302477
35°	93960
40°	25247
45°	8838
50°	2115
55°	688
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8838 cd/sqm

TEST NUMBER: P1258205

CATALOG NUMBER: P3AS20R509040D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.5	14.5
10°-20°	905.7	35.9
20°-30°	951.9	37.7
30°-40°	272.4	10.8
40°-50°	26.6	1.1
50°-60°	2.2	0.1
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2223.0	88.0
0°-40°	2495.4	98.8
0°-60°	2524.2	100.0
0°-90°	2525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2525.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4024	
5°	3902	365
15°	3269	906
25°	2176	952
35°	351	272
45°	28	27
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1258205

CATALOG NUMBER: P3AS20R509040D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4024.0
1°	4017.8
2°	4000.0
3°	3974.1
4°	3939.4
5°	3902.0
6°	3861.9
7°	3819.1
8°	3779.0
9°	3732.7
10°	3681.0
11°	3621.3
12°	3552.7
13°	3467.2
14°	3374.6
15°	3268.6
16°	3156.3
17°	3047.6
18°	2936.3
19°	2838.3
20°	2751.0
21°	2667.2
22°	2571.9
23°	2462.3
24°	2334.0
25°	2176.4
26°	2005.3
27°	1814.7
28°	1624.9
29°	1420.0
30°	1194.6
31°	983.5
32°	789.3
32.5°	704.7
33°	619.1
34°	474.8
35°	351.0
36°	257.5
37°	191.5
37.5°	165.7
38°	143.4
39°	111.4
40°	88.2
42.5°	49.9
45°	28.5

TEST NUMBER: P1258205

CATALOG NUMBER: P3AS20R509040D010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	16.0
50°	6.2
52.5°	2.7
55°	1.8
57.5°	1.8
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)