

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257592

Luminaire Tested: P3AS13R659040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 725.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257592

CATALOG NUMBER: P3AS13R659040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257592

CATALOG NUMBER: P3AS13R659040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		78
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		57
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184283
5°	179705
10°	167332
15°	149967
20°	129511
25°	107740
30°	84950
35°	62961
40°	43396
45°	26918
50°	14635
55°	9175
60°	7806
65°	7057
70°	6027
75°	5338
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26918 cd/sqm

TEST NUMBER: P1257592

CATALOG NUMBER: P3AS13R659040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.9	10.5
10°-20°	183.6	25.3
20°-30°	203.0	28.0
30°-40°	147.5	20.3
40°-50°	69.1	9.5
50°-60°	23.3	3.2
60°-70°	13.4	1.9
70°-80°	7.0	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.4	63.8
0°-40°	609.9	84.1
0°-60°	702.3	96.9
0°-90°	725.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	840	
5°	816	76
15°	661	184
25°	445	203
35°	235	147
45°	87	69
55°	24	23
65°	14	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1257592

CATALOG NUMBER: P3AS13R659040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	840.4
2.5°	835.2
5°	816.4
7.5°	788.1
10°	751.5
12.5°	708.7
15°	660.6
17.5°	608.3
20°	555.0
22.5°	499.6
25°	445.3
27.5°	389.9
30°	335.5
32.5°	283.3
35°	235.2
37.5°	191.3
40°	151.6
42.5°	116.0
45°	86.8
47.5°	62.7
50°	42.9
52.5°	29.3
55°	24.0
57.5°	20.9
60°	17.8
62.5°	15.7
65°	13.6
67.5°	11.5
70°	9.4
72.5°	8.4
75°	6.3
77.5°	5.2
80°	4.2
82.5°	3.1
85°	2.1
87.5°	1.0
90°	0.0

(END OF REPORT)