

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257606

Luminaire Tested: P3AS13R709040DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709040DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1053.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257606

CATALOG NUMBER: P3AS13R709040DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1257606

CATALOG NUMBER: P3AS13R709040DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	82		89	85	81		86	83	80		84	81	79
4	94	86	80	75		93	85	79	75		83	78	74		81	76	73		79	75	72
5	89	80	73	69		87	79	73	68		77	72	68		75	71	67		74	70	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	53		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	50	46		66	56	50	46		55	50	46		55	49	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203843
5°	201408
10°	195588
15°	187311
20°	175459
25°	159396
30°	137692
35°	109727
40°	79921
45°	52533
50°	24630
55°	7608
60°	7324
65°	7057
70°	6732
75°	7117
80°	6566
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 52533 cd/sqm

TEST NUMBER: P1257606

CATALOG NUMBER: P3AS13R709040DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	8.2
10°-20°	230.9	21.9
20°-30°	300.1	28.5
30°-40°	254.7	24.2
40°-50°	131.3	12.5
50°-60°	25.3	2.4
60°-70°	13.7	1.3
70°-80°	8.4	0.8
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.2	58.6
0°-40°	871.9	82.8
0°-60°	1028.5	97.7
0°-90°	1053.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1053.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	930	
5°	915	86
15°	825	231
25°	659	300
35°	410	255
45°	169	131
55°	20	25
65°	14	14
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1257606

CATALOG NUMBER: P3AS13R709040DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	929.6
2.5°	926.5
5°	915.0
7.5°	898.3
10°	878.4
12.5°	853.3
15°	825.1
17.5°	790.6
20°	751.9
22.5°	707.9
25°	658.8
27.5°	603.4
30°	543.8
32.5°	477.9
35°	409.9
37.5°	343.0
40°	279.2
42.5°	219.6
45°	169.4
47.5°	124.4
50°	72.2
52.5°	31.4
55°	19.9
57.5°	18.8
60°	16.7
62.5°	15.7
65°	13.6
67.5°	12.5
70°	10.5
72.5°	9.4
75°	8.4
77.5°	6.3
80°	5.2
82.5°	3.1
85°	2.1
87.5°	1.0
90°	0.0

(END OF REPORT)