

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257635

Luminaire Tested: P3AS17R129040DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R129040DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1189.0 lumens
Efficiency: N/A
Efficacy: 51.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257635
CATALOG NUMBER: P3AS17R129040DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1257635
 CATALOG NUMBER: P3AS17R129040DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1015708
5°	901605
10°	626130
15°	370286
20°	210882
25°	120563
30°	66694
35°	35576
40°	19665
45°	10668
50°	6652
55°	5238
60°	4517
65°	4151
70°	3654
75°	3897
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10668 cd/sqm



TEST NUMBER: P1257635
 CATALOG NUMBER: P3AS17R129040DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.3	29.3
10°-20°	459.7	38.7
20°-30°	236.7	19.9
30°-40°	88.9	7.5
40°-50°	29.1	2.4
50°-60°	12.5	1.1
60°-70°	7.9	0.7
70°-80°	4.7	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1044.7	87.9
0°-40°	1133.5	95.3
0°-60°	1175.2	98.8
0°-90°	1189.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1189.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4632	
5°	4096	348
15°	1631	460
25°	498	237
35°	133	89
45°	34	29
55°	14	13
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1257635
CATALOG NUMBER: P3AS17R129040DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4632.0
1°	4622.9
2°	4562.2
3°	4446.5
4°	4294.1
5°	4096.0
6°	3871.5
7°	3625.2
8°	3351.5
9°	3081.2
10°	2812.0
12.5°	2163.7
15°	1631.1
17.5°	1221.0
20°	903.7
22.5°	674.6
25°	498.3
27.5°	363.1
30°	263.4
32.5°	186.7
35°	132.9
37.5°	95.1
40°	68.7
42.5°	49.3
45°	34.4
47.5°	25.2
50°	19.5
52.5°	16.0
55°	13.7
57.5°	11.5
60°	10.3
62.5°	9.2
65°	8.0
67.5°	6.9
70°	5.7
72.5°	5.7
75°	4.6
77.5°	3.4
80°	2.3
82.5°	2.3
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)