

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257643

Luminaire Tested: P3AS17R129040DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R129040DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 705.0 lumens
Efficiency: N/A
Efficacy: 30.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257643
CATALOG NUMBER: P3AS17R129040DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1257643
 CATALOG NUMBER: P3AS17R129040DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	304011
5°	280981
10°	224333
15°	169445
20°	129045
25°	98328
30°	70441
35°	45963
40°	28196
45°	17056
50°	11326
55°	8755
60°	7543
65°	6538
70°	5898
75°	5846
80°	4293
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17056 cd/sqm



TEST NUMBER: P1257643
 CATALOG NUMBER: P3AS17R129040DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	16.0
10°-20°	208.6	29.6
20°-30°	185.7	26.3
30°-40°	109.9	15.6
40°-50°	45.1	6.4
50°-60°	21.2	3.0
60°-70°	12.9	1.8
70°-80°	6.8	1.0
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	507.4	72.0
0°-40°	617.4	87.6
0°-60°	683.7	97.0
0°-90°	705.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1386	
5°	1276	113
15°	746	209
25°	406	186
35°	172	110
45°	55	45
55°	23	21
65°	13	13
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1257643
CATALOG NUMBER: P3AS17R129040DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1386.4
1°	1383.0
2°	1372.7
3°	1352.1
4°	1317.7
5°	1276.5
6°	1231.9
7°	1179.2
8°	1124.2
9°	1068.1
10°	1007.5
12.5°	868.9
15°	746.4
17.5°	641.1
20°	553.0
22.5°	475.1
25°	406.4
27.5°	340.0
30°	278.2
32.5°	222.1
35°	171.7
37.5°	131.7
40°	98.5
42.5°	73.3
45°	55.0
47.5°	42.4
50°	33.2
52.5°	27.5
55°	22.9
57.5°	19.5
60°	17.2
62.5°	14.9
65°	12.6
67.5°	11.4
70°	9.2
72.5°	8.0
75°	6.9
77.5°	4.6
80°	3.4
82.5°	2.3
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)