

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258231

Luminaire Tested: P3AS20R559040D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559040D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2420.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258231

CATALOG NUMBER: P3AS20R559040D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1258231

CATALOG NUMBER: P3AS20R559040D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		86
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	69	65	73	68	65		72	67	64		71
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	671196
5°	664955
10°	691682
15°	682070
20°	628958
25°	511771
30°	310833
35°	107586
40°	30715
45°	14668
50°	6209
55°	2791
60°	3201
65°	2854
70°	2308
75°	3050
80°	2273
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14668 cd/sqm

TEST NUMBER: P1258231

CATALOG NUMBER: P3AS20R559040D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.0	12.1
10°-20°	835.0	34.5
20°-30°	930.9	38.5
30°-40°	304.5	12.6
40°-50°	40.1	1.7
50°-60°	8.5	0.4
60°-70°	5.0	0.2
70°-80°	3.1	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2058.0	85.0
0°-40°	2362.6	97.6
0°-60°	2411.2	99.6
0°-90°	2420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3061	
5°	3021	292
15°	3004	835
25°	2115	931
35°	402	305
45°	47	40
55°	7	8
65°	6	5
75°	4	3
85°	0	1
90°	0	

TEST NUMBER: P1258231

CATALOG NUMBER: P3AS20R559040D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3060.9
2.5°	3039.1
5°	3020.9
7.5°	3064.6
10°	3106.4
12.5°	3084.6
15°	3004.5
17.5°	2877.2
20°	2695.3
22.5°	2444.4
25°	2115.2
27.5°	1696.9
30°	1227.6
32.5°	753.0
35°	401.9
37.5°	203.7
40°	107.3
42.5°	69.1
45°	47.3
47.5°	32.7
50°	18.2
52.5°	10.9
55°	7.3
57.5°	7.3
60°	7.3
62.5°	5.5
65°	5.5
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)