

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257691

Luminaire Tested: P3AS17R209040DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209040DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1736.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257691

CATALOG NUMBER: P3AS17R209040DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257691

CATALOG NUMBER: P3AS17R209040DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2633364
5°	2217186
10°	1384833
15°	517733
20°	177722
25°	74061
30°	34891
35°	15633
40°	7385
45°	3783
50°	1399
55°	268
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3783 cd/sqm

TEST NUMBER: P1257691

CATALOG NUMBER: P3AS17R209040DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	837.6	48.3
10°-20°	690.0	39.7
20°-30°	156.8	9.0
30°-40°	39.9	2.3
40°-50°	10.0	0.6
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1684.4	97.0
0°-40°	1724.3	99.3
0°-60°	1735.6	100.0
0°-90°	1736.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1736.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12009	
5°	10073	838
15°	2281	690
25°	306	157
35°	58	40
45°	12	10
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1257691

CATALOG NUMBER: P3AS17R209040DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	12009.1
1°	11907.3
2°	11607.3
3°	11177.0
4°	10648.9
5°	10072.7
6°	9430.6
7°	8721.9
8°	7895.2
9°	7076.0
10°	6219.4
11°	5307.8
12°	4397.6
13°	3626.6
14°	2889.4
15°	2280.6
16°	1800.0
17°	1419.9
18°	1141.0
19°	927.9
20°	761.6
21°	636.7
22°	531.5
23°	441.9
24°	368.6
25°	306.1
27.5°	200.2
30°	137.8
32.5°	84.8
35°	58.4
37.5°	37.3
40°	25.8
42.5°	17.6
45°	12.2
47.5°	8.1
50°	4.1
52.5°	2.0
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1257691

CATALOG NUMBER: P3AS17R209040DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)