

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257708

Luminaire Tested: P3AS17R259040DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259040DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1763.1 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257708
CATALOG NUMBER: P3AS17R259040DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1257708
 CATALOG NUMBER: P3AS17R259040DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	698.6	39.6
10°-20°	833.4	47.3
20°-30°	187.9	10.7
30°-40°	30.4	1.7
40°-50°	5.5	0.3
50°-60°	3.0	0.2
60°-70°	2.6	0.1
70°-80°	1.5	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1719.9	97.5
0°-40°	1750.3	99.3
0°-60°	1758.8	99.8
0°-90°	1763.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1763.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8596	
5°	7942	699
15°	2995	833
25°	367	188
35°	36	30
45°	6	6
55°	3	3
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1257708
CATALOG NUMBER: P3AS17R259040DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	8595.8
1°	8582.0
2°	8512.7
3°	8385.3
4°	8192.8
5°	7942.1
6°	7642.9
7°	7318.8
8°	6947.6
9°	6541.8
10°	6088.8
11°	5566.7
12°	4965.5
13°	4336.7
14°	3662.2
15°	2994.6
17.5°	1706.4
20°	957.1
22.5°	577.6
25°	367.0
27.5°	225.8
30°	131.6
32.5°	69.3
35°	36.0
37.5°	23.5
40°	15.2
42.5°	9.7
45°	5.5
47.5°	4.2
50°	4.2
52.5°	4.2
55°	2.8
57.5°	2.8
60°	2.8
62.5°	2.8
65°	2.8
67.5°	2.8
70°	1.4
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1257708
CATALOG NUMBER: P3AS17R259040DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)