

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257792

Luminaire Tested: P3AS17R359040DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359040DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 898.0 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257792

CATALOG NUMBER: P3AS17R359040DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1257792

CATALOG NUMBER: P3AS17R359040DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	288639
5°	281531
10°	257377
15°	218458
20°	172938
25°	130798
30°	95230
35°	64407
40°	39588
45°	22731
50°	13680
55°	11087
60°	9692
65°	8613
70°	7117
75°	7032
80°	6945
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22731 cd/sqm

TEST NUMBER: P1257792

CATALOG NUMBER: P3AS17R359040DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	13.2
10°-20°	265.3	29.5
20°-30°	248.2	27.6
30°-40°	151.9	16.9
40°-50°	59.9	6.7
50°-60°	26.4	2.9
60°-70°	16.4	1.8
70°-80°	8.8	1.0
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	631.7	70.3
0°-40°	783.6	87.3
0°-60°	869.8	96.9
0°-90°	898.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	898.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1316	
5°	1279	118
15°	962	265
25°	541	248
35°	241	152
45°	73	60
55°	29	26
65°	17	16
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P1257792

CATALOG NUMBER: P3AS17R359040DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1316.3
1°	1317.7
2°	1313.5
3°	1305.2
4°	1292.8
5°	1279.0
6°	1261.0
7°	1240.3
8°	1215.4
9°	1187.7
10°	1155.9
11°	1122.7
12°	1086.8
13°	1048.1
14°	1005.2
15°	962.3
17.5°	851.7
20°	741.1
22.5°	634.6
25°	540.6
27.5°	453.5
30°	376.1
32.5°	304.2
35°	240.6
37.5°	183.9
40°	138.3
42.5°	99.6
45°	73.3
47.5°	52.5
50°	40.1
52.5°	33.2
55°	29.0
57.5°	24.9
60°	22.1
62.5°	19.4
65°	16.6
67.5°	13.8
70°	11.1
72.5°	9.7
75°	8.3
77.5°	6.9
80°	5.5
82.5°	4.1
85°	2.8
87.5°	1.4



TEST NUMBER: P1257792

CATALOG NUMBER: P3AS17R359040DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)