

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258362

Luminaire Tested: P3AS24R159040D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R159040D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 627.0 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258362

CATALOG NUMBER: P3AS24R159040D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1258362

CATALOG NUMBER: P3AS24R159040D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270373
5°	249900
10°	199506
15°	150716
20°	114763
25°	87465
30°	62643
35°	40877
40°	25076
45°	15164
50°	10064
55°	7799
60°	6710
65°	5811
70°	5193
75°	5168
80°	3915
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15164 cd/sqm

TEST NUMBER: P1258362

CATALOG NUMBER: P3AS24R159040D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.6	16.0
10°-20°	185.6	29.6
20°-30°	165.2	26.3
30°-40°	97.7	15.6
40°-50°	40.1	6.4
50°-60°	18.8	3.0
60°-70°	11.4	1.8
70°-80°	6.0	1.0
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.3	72.0
0°-40°	549.1	87.6
0°-60°	608.0	97.0
0°-90°	627.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	627.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1233	
5°	1135	101
15°	664	186
25°	362	165
35°	153	98
45°	49	40
55°	20	19
65°	11	11
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1258362

CATALOG NUMBER: P3AS24R159040D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1233.0
1°	1230.0
2°	1220.8
3°	1202.5
4°	1171.9
5°	1135.3
6°	1095.6
7°	1048.7
8°	999.9
9°	950.0
10°	896.0
12.5°	772.8
15°	663.9
17.5°	570.2
20°	491.8
22.5°	422.5
25°	361.5
27.5°	302.4
30°	247.4
32.5°	197.5
35°	152.7
37.5°	117.1
40°	87.6
42.5°	65.2
45°	48.9
47.5°	37.7
50°	29.5
52.5°	24.4
55°	20.4
57.5°	17.3
60°	15.3
62.5°	13.2
65°	11.2
67.5°	10.2
70°	8.1
72.5°	7.1
75°	6.1
77.5°	4.1
80°	3.1
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)