

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258377

Luminaire Tested: P3AS24R209040D010 E3D1B

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209040D010 E3D1B
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3D1B TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2604.0 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258377

CATALOG NUMBER: P3AS24R209040D010 E3D1B

Luminous Intensity Polar Plot



TEST NUMBER: P1258377

CATALOG NUMBER: P3AS24R209040D010 E3D1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3950056
5°	3325767
10°	2077249
15°	776599
20°	266560
25°	111103
30°	52337
35°	23450
40°	11078
45°	5675
50°	2081
55°	382
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5675 cd/sqm

TEST NUMBER: P1258377

CATALOG NUMBER: P3AS24R209040D010 E3D1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1256.4	48.3
10°-20°	1034.9	39.7
20°-30°	235.2	9.0
30°-40°	59.9	2.3
40°-50°	15.0	0.6
50°-60°	1.9	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2526.6	97.0
0°-40°	2586.4	99.3
0°-60°	2603.4	100.0
0°-90°	2604.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2604.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18014	
5°	15109	###
15°	3421	1035
25°	459	235
35°	88	60
45°	18	15
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1258377

CATALOG NUMBER: P3AS24R209040D010 E3D1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	18013.7
1°	17861.0
2°	17411.0
3°	16765.5
4°	15973.4
5°	15109.0
6°	14145.8
7°	13082.9
8°	11842.8
9°	10614.0
10°	9329.1
11°	7961.7
12°	6596.4
13°	5439.8
14°	4334.2
15°	3420.9
16°	2700.1
17°	2129.9
18°	1711.5
19°	1391.8
20°	1142.3
21°	955.0
22°	797.2
23°	662.8
24°	552.8
25°	459.2
27.5°	300.3
30°	206.7
32.5°	127.3
35°	87.6
37.5°	56.0
40°	38.7
42.5°	26.5
45°	18.3
47.5°	12.2
50°	6.1
52.5°	3.1
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1258377

CATALOG NUMBER: P3AS24R209040D010 E3D1B

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)