

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257805

Luminaire Tested: P3AS17R409040DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409040DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1939.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257805
CATALOG NUMBER: P3AS17R409040DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1257805
 CATALOG NUMBER: P3AS17R409040DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	988364
5°	981221
10°	955538
15°	853558
20°	565976
25°	212020
30°	56718
35°	22165
40°	7958
45°	3783
50°	1160
55°	535
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3783 cd/sqm



TEST NUMBER: P1257805
 CATALOG NUMBER: P3AS17R409040DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.7	21.7
10°-20°	996.2	51.4
20°-30°	451.8	23.3
30°-40°	58.6	3.0
40°-50°	10.1	0.5
50°-60°	1.2	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1868.7	96.4
0°-40°	1927.3	99.4
0°-60°	1938.6	100.0
0°-90°	1939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4507	
5°	4458	421
15°	3760	996
25°	876	452
35°	83	59
45°	12	10
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1257805
CATALOG NUMBER: P3AS17R409040DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4507.3
1°	4504.5
2°	4497.7
3°	4487.6
4°	4474.7
5°	4457.7
6°	4438.0
7°	4413.6
8°	4383.7
9°	4343.0
10°	4291.4
11°	4231.0
12°	4150.2
13°	4050.4
14°	3920.1
15°	3759.9
16°	3555.6
17°	3322.7
18°	3043.1
19°	2747.8
20°	2425.4
21°	2102.9
22°	1785.3
23°	1468.9
24°	1158.0
25°	876.3
26°	648.9
27°	475.2
28°	357.1
29°	277.6
30°	224.0
31°	185.3
32°	154.8
32.5°	141.2
33°	127.6
34°	103.9
35°	82.8
36°	65.2
37°	51.6
37.5°	46.2
38°	40.7
39°	33.9
40°	27.8
42.5°	18.3
45°	12.2



TEST NUMBER: P1257805
CATALOG NUMBER: P3AS17R409040DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	7.5
50°	3.4
52.5°	1.4
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)