

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258379

Luminaire Tested: P3AS24R209040D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209040D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2624.1 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258379
CATALOG NUMBER: P3AS24R209040D010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1258379
 CATALOG NUMBER: P3AS24R209040D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	99	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	99	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	93	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	86	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4075375
5°	3537279
10°	2185664
15°	759142
20°	233120
25°	82408
30°	30511
35°	12234
40°	6527
45°	2574
50°	1433
55°	1606
60°	1842
65°	1090
70°	1346
75°	1779
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2574 cd/sqm



TEST NUMBER: P1258379
 CATALOG NUMBER: P3AS24R209040D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1333.7	50.8
10°-20°	1058.2	40.3
20°-30°	183.2	7.0
30°-40°	33.3	1.3
40°-50°	7.6	0.3
50°-60°	3.8	0.1
60°-70°	2.3	0.1
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2575.1	98.1
0°-40°	2608.4	99.4
0°-60°	2619.8	99.8
0°-90°	2624.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2624.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18585	
5°	16070	###
15°	3344	1058
25°	341	183
35°	46	33
45°	8	8
55°	4	4
65°	2	2
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1258379
CATALOG NUMBER: P3AS24R209040D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	18585.2
1°	18495.9
2°	18142.8
3°	17575.7
4°	16911.1
5°	16069.9
6°	15106.2
7°	13984.6
8°	12707.2
9°	11272.0
10°	9816.0
12.5°	6191.6
15°	3344.0
17.5°	1786.2
20°	999.0
22.5°	571.2
25°	340.6
27.5°	207.7
30°	120.5
32.5°	70.6
35°	45.7
37.5°	31.2
40°	22.8
42.5°	14.5
45°	8.3
47.5°	4.2
50°	4.2
52.5°	4.2
55°	4.2
57.5°	4.2
60°	4.2
62.5°	2.1
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)