

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258396

Luminaire Tested: P3AS24R209040D010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209040D010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1017.0 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258396
CATALOG NUMBER: P3AS24R209040D010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1258396
 CATALOG NUMBER: P3AS24R209040D010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361660
5°	337331
10°	279932
15°	214053
20°	160641
25°	120951
30°	89431
35°	62506
40°	42852
45°	29709
50°	25517
55°	25194
60°	26270
65°	26410
70°	26864
75°	27874
80°	30181
85°	30192

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 35279 cd/sqm



TEST NUMBER: P1258396
 CATALOG NUMBER: P3AS24R209040D010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	13.5
10°-20°	262.2	25.8
20°-30°	230.6	22.7
30°-40°	148.9	14.6
40°-50°	78.9	7.8
50°-60°	59.3	5.8
60°-70°	50.4	5.0
70°-80°	35.5	3.5
80°-90°	13.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.1	62.0
0°-40°	779.0	76.6
0°-60°	917.2	90.2
0°-90°	1017.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1017.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1649	
5°	1532	137
15°	943	262
25°	500	231
35°	234	149
45°	96	79
55°	66	59
65°	51	50
75°	33	36
85°	12	14
90°	0	



TEST NUMBER: P1258396
CATALOG NUMBER: P3AS24R209040D010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1649.3
2.5°	1616.4
5°	1532.5
7.5°	1403.8
10°	1257.2
12.5°	1095.5
15°	942.9
17.5°	805.2
20°	688.4
22.5°	589.7
25°	499.9
27.5°	422.0
30°	353.2
32.5°	290.3
35°	233.5
37.5°	188.6
40°	149.7
42.5°	119.7
45°	95.8
47.5°	83.8
50°	74.8
52.5°	68.8
55°	65.9
57.5°	62.9
60°	59.9
62.5°	53.9
65°	50.9
67.5°	47.9
70°	41.9
72.5°	38.9
75°	32.9
77.5°	29.9
80°	23.9
82.5°	21.0
85°	12.0
87.5°	6.0
90°	0.0

(END OF REPORT)