

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257835

Luminaire Tested: P3AS17R459040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 759.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257835

CATALOG NUMBER: P3AS17R459040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257835

CATALOG NUMBER: P3AS17R459040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285021
5°	278340
10°	255885
15°	216800
20°	168225
25°	117587
30°	74062
35°	43607
40°	24675
45°	12001
50°	4162
55°	3364
60°	3289
65°	3165
70°	3077
75°	2881
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12001 cd/sqm

TEST NUMBER: P1257835

CATALOG NUMBER: P3AS17R459040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.1	15.4
10°-20°	262.3	34.6
20°-30°	222.7	29.3
30°-40°	106.2	14.0
40°-50°	32.0	4.2
50°-60°	8.1	1.1
60°-70°	6.1	0.8
70°-80°	3.6	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	602.0	79.3
0°-40°	708.2	93.3
0°-60°	748.3	98.6
0°-90°	759.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1264	117
15°	955	262
25°	486	223
35°	163	106
45°	39	32
55°	9	8
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1257835

CATALOG NUMBER: P3AS17R459040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1299.8
2.5°	1291.7
5°	1264.5
7.5°	1217.7
10°	1149.2
12.5°	1058.2
15°	955.0
17.5°	840.3
20°	720.9
22.5°	599.4
25°	486.0
27.5°	382.8
30°	292.5
32.5°	219.9
35°	162.9
37.5°	120.1
40°	86.2
42.5°	59.7
45°	38.7
47.5°	21.7
50°	12.2
52.5°	9.5
55°	8.8
57.5°	8.1
60°	7.5
62.5°	6.8
65°	6.1
67.5°	5.4
70°	4.8
72.5°	4.1
75°	3.4
77.5°	2.7
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)