

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258438

Luminaire Tested: P3AS24R309040D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309040D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2622.9 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258438

CATALOG NUMBER: P3AS24R309040D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1258438

CATALOG NUMBER: P3AS24R309040D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97
3	108	103	100	97	106	102	99	96	99	97	95		97	95	93		95
4	105	99	95	92	103	98	95	92	96	93	91		94	92	90		93
5	101	96	92	89	100	95	91	88	93	90	87		92	89	87		90
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88
7	96	89	85	82	95	89	85	82	88	84	82		87	84	81		86
8	93	87	83	80	92	86	82	80	85	82	79		84	81	79		84
9	91	84	80	77	90	84	80	77	83	79	77		82	79	77		82
10	88	82	78	75	88	81	78	75	81	77	75		80	77	75		80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2086938
5°	2059713
10°	1798319
15°	1143026
20°	452869
25°	151267
30°	70391
35°	31882
40°	12252
45°	5985
50°	1740
55°	765
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5985 cd/sqm

TEST NUMBER: P1258438

CATALOG NUMBER: P3AS24R309040D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	855.5	32.6
10°-20°	1326.7	50.6
20°-30°	342.1	13.0
30°-40°	80.3	3.1
40°-50°	15.7	0.6
50°-60°	1.8	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2524.3	96.2
0°-40°	2604.6	99.3
0°-60°	2622.1	100.0
0°-90°	2622.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2622.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9517	
5°	9357	856
15°	5035	1327
25°	625	342
35°	119	80
45°	19	16
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1258438

CATALOG NUMBER: P3AS24R309040D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	9517.2
1°	9510.1
2°	9487.7
3°	9462.2
4°	9424.5
5°	9357.3
6°	9248.4
7°	9067.2
8°	8819.7
9°	8497.0
10°	8076.4
11°	7576.5
12°	7030.7
13°	6402.5
14°	5744.7
15°	5035.0
16°	4339.6
17°	3669.6
18°	3027.1
19°	2437.6
20°	1940.7
21°	1527.3
22°	1201.5
23°	951.0
24°	761.6
25°	625.2
26°	521.3
27°	442.9
28°	382.8
29°	327.9
30°	278.0
32.5°	175.1
35°	119.1
37.5°	74.3
40°	42.8
42.5°	28.5
45°	19.3
47.5°	11.2
50°	5.1
52.5°	2.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0

TEST NUMBER: P1258438

CATALOG NUMBER: P3AS24R309040D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)