

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258439

Luminaire Tested: P3AS24R309040D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258439
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309040D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2622.9 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258439

CATALOG NUMBER: P3AS24R309040D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1258439

CATALOG NUMBER: P3AS24R309040D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2086938
5°	2059713
10°	1798319
15°	1143026
20°	452869
25°	151267
30°	70391
35°	31882
40°	12252
45°	5985
50°	1740
55°	765
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5985 cd/sqm

TEST NUMBER: P1258439

CATALOG NUMBER: P3AS24R309040D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	855.5	32.6
10°-20°	1326.7	50.6
20°-30°	342.1	13.0
30°-40°	80.3	3.1
40°-50°	15.7	0.6
50°-60°	1.8	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2524.3	96.2
0°-40°	2604.6	99.3
0°-60°	2622.1	100.0
0°-90°	2622.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2622.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9517	
5°	9357	856
15°	5035	1327
25°	625	342
35°	119	80
45°	19	16
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1258439

CATALOG NUMBER: P3AS24R309040D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	9517.2
1°	9510.1
2°	9487.7
3°	9462.2
4°	9424.5
5°	9357.3
6°	9248.4
7°	9067.2
8°	8819.7
9°	8497.0
10°	8076.4
11°	7576.5
12°	7030.7
13°	6402.5
14°	5744.7
15°	5035.0
16°	4339.6
17°	3669.6
18°	3027.1
19°	2437.6
20°	1940.7
21°	1527.3
22°	1201.5
23°	951.0
24°	761.6
25°	625.2
26°	521.3
27°	442.9
28°	382.8
29°	327.9
30°	278.0
32.5°	175.1
35°	119.1
37.5°	74.3
40°	42.8
42.5°	28.5
45°	19.3
47.5°	11.2
50°	5.1
52.5°	2.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0



TEST NUMBER: P1258439

CATALOG NUMBER: P3AS24R309040D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)