

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257851

Luminaire Tested: P3AS17R459040DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257851
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459040DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1548.0 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257851

CATALOG NUMBER: P3AS17R459040DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257851

CATALOG NUMBER: P3AS17R459040DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	581335
5°	567707
10°	521856
15°	442182
20°	343076
25°	239820
30°	151087
35°	88927
40°	50323
45°	24468
50°	8494
55°	6881
60°	6666
65°	6486
70°	6219
75°	5846
80°	5304
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24468 cd/sqm

TEST NUMBER: P1257851

CATALOG NUMBER: P3AS17R459040DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.7	15.4
10°-20°	534.9	34.6
20°-30°	454.2	29.3
30°-40°	216.7	14.0
40°-50°	65.2	4.2
50°-60°	16.5	1.1
60°-70°	12.3	0.8
70°-80°	7.3	0.5
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1227.8	79.3
0°-40°	1444.5	93.3
0°-60°	1526.3	98.6
0°-90°	1548.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1548.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2651	
5°	2579	239
15°	1948	535
25°	991	454
35°	332	217
45°	79	65
55°	18	17
65°	12	12
75°	7	7
85°	1	2
90°	0	

TEST NUMBER: P1257851

CATALOG NUMBER: P3AS17R459040DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2651.1
2.5°	2634.5
5°	2579.1
7.5°	2483.6
10°	2343.7
12.5°	2158.2
15°	1947.8
17.5°	1713.8
20°	1470.2
22.5°	1222.4
25°	991.2
27.5°	780.8
30°	596.7
32.5°	448.5
35°	332.2
37.5°	245.0
40°	175.8
42.5°	121.8
45°	78.9
47.5°	44.3
50°	24.9
52.5°	19.4
55°	18.0
57.5°	16.6
60°	15.2
62.5°	13.8
65°	12.5
67.5°	11.1
70°	9.7
72.5°	8.3
75°	6.9
77.5°	5.5
80°	4.2
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)