

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257870

Luminaire Tested: P3AS17R509040DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257870  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R509040DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 595.0 lumens  
Efficiency: N/A  
Efficacy: 28.1 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257870  
CATALOG NUMBER: P3AS17R509040DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1257870  
 CATALOG NUMBER: P3AS17R509040DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69				69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58				58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53				53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50				50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46				46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43				43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120911
5°	119128
10°	113870
15°	105449
20°	94765
25°	83303
30°	70846
35°	57447
40°	43167
45°	27786
50°	13202
55°	10399
60°	9824
65°	9184
70°	8271
75°	7456
80°	6819
85°	6793

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27786 cd/sqm



TEST NUMBER: P1257870  
 CATALOG NUMBER: P3AS17R509040DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.7	8.5
10°-20°	129.5	21.8
20°-30°	157.4	26.4
30°-40°	133.5	22.4
40°-50°	69.3	11.6
50°-60°	25.0	4.2
60°-70°	17.3	2.9
70°-80°	9.4	1.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.6	56.7
0°-40°	471.0	79.2
0°-60°	565.4	95.0
0°-90°	595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	551	
5°	541	51
15°	464	130
25°	344	157
35°	215	133
45°	90	69
55°	27	25
65°	18	17
75°	9	9
85°	3	3
90°	0	



TEST NUMBER: P1257870  
CATALOG NUMBER: P3AS17R509040DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	551.4
2.5°	549.4
5°	541.2
7.5°	529.0
10°	511.4
12.5°	488.9
15°	464.5
17.5°	436.7
20°	406.1
22.5°	374.9
25°	344.3
27.5°	312.4
30°	279.8
32.5°	247.2
35°	214.6
37.5°	182.7
40°	150.8
42.5°	120.2
45°	89.6
47.5°	59.8
50°	38.7
52.5°	29.9
55°	27.2
57.5°	24.4
60°	22.4
62.5°	19.7
65°	17.7
67.5°	14.9
70°	12.9
72.5°	10.9
75°	8.8
77.5°	6.8
80°	5.4
82.5°	4.1
85°	2.7
87.5°	1.4
90°	0.0

(END OF REPORT)