

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258566

Luminaire Tested: P3AS24R509040D010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258566  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R509040D010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 752.0 lumens  
Efficiency: N/A  
Efficacy: 26.1 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258566  
CATALOG NUMBER: P3AS24R509040D010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1258566

CATALOG NUMBER: P3AS24R509040D010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	218711
5°	212832
10°	196256
15°	172600
20°	144399
25°	114515
30°	84013
35°	57768
40°	36697
45°	20529
50°	11121
55°	9328
60°	8026
65°	7368
70°	6540
75°	6015
80°	5177
85°	5032

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20529 cd/sqm



TEST NUMBER: P1258566  
 CATALOG NUMBER: P3AS24R509040D010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.6	11.9
10°-20°	210.6	28.0
20°-30°	215.4	28.6
30°-40°	136.6	18.2
40°-50°	54.4	7.2
50°-60°	22.0	2.9
60°-70°	14.1	1.9
70°-80°	7.2	1.0
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.5	68.6
0°-40°	652.1	86.7
0°-60°	728.5	96.9
0°-90°	752.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	752.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	997	
5°	967	90
15°	760	211
25°	473	215
35°	216	137
45°	66	54
55°	24	22
65°	14	14
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1258566  
CATALOG NUMBER: P3AS24R509040D010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	997.4
2.5°	990.3
5°	966.9
7.5°	930.3
10°	881.4
12.5°	823.4
15°	760.3
17.5°	691.1
20°	618.8
22.5°	546.5
25°	473.3
27.5°	400.0
30°	331.8
32.5°	270.7
35°	215.8
37.5°	169.0
40°	128.2
42.5°	94.7
45°	66.2
47.5°	44.8
50°	32.6
52.5°	27.5
55°	24.4
57.5°	21.4
60°	18.3
62.5°	16.3
65°	14.2
67.5°	12.2
70°	10.2
72.5°	8.1
75°	7.1
77.5°	5.1
80°	4.1
82.5°	3.1
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)