

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257934

Luminaire Tested: P3AS17R609040DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257934  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R609040DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 494.0 lumens  
Efficiency: N/A  
Efficacy: 23.3 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257934  
CATALOG NUMBER: P3AS17R609040DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1257934  
 CATALOG NUMBER: P3AS17R609040DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	125187
5°	122386
10°	114583
15°	102793
20°	88394
25°	73093
30°	57756
35°	42884
40°	29541
45°	18514
50°	10200
55°	5964
60°	5350
65°	4566
70°	3911
75°	4067
80°	3410
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18514 cd/sqm



TEST NUMBER: P1257934  
 CATALOG NUMBER: P3AS17R609040DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.8	10.5
10°-20°	125.8	25.5
20°-30°	137.9	27.9
30°-40°	100.5	20.3
40°-50°	47.4	9.6
50°-60°	15.6	3.1
60°-70°	8.8	1.8
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.5	63.9
0°-40°	415.9	84.2
0°-60°	478.9	97.0
0°-90°	494.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	494.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	571	
5°	556	52
15°	453	126
25°	302	138
35°	160	100
45°	60	47
55°	16	16
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1257934  
CATALOG NUMBER: P3AS17R609040DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	570.9
2.5°	567.5
5°	556.0
7.5°	538.3
10°	514.6
12.5°	486.1
15°	452.8
17.5°	416.8
20°	378.8
22.5°	340.1
25°	302.1
27.5°	264.1
30°	228.1
32.5°	193.5
35°	160.2
37.5°	130.3
40°	103.2
42.5°	79.4
45°	59.7
47.5°	43.4
50°	29.9
52.5°	19.7
55°	15.6
57.5°	13.6
60°	12.2
62.5°	10.2
65°	8.8
67.5°	7.5
70°	6.1
72.5°	5.4
75°	4.8
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)