

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258575

Luminaire Tested: P3AS24R559040D010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258575  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R559040D010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2765.0 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258575  
CATALOG NUMBER: P3AS24R559040D010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1258575  
 CATALOG NUMBER: P3AS24R559040D010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	85	83	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	766890
5°	759760
10°	790277
15°	779323
20°	718636
25°	584719
30°	355169
35°	122924
40°	35094
45°	16746
50°	7096
55°	3173
60°	3640
65°	3217
70°	2693
75°	3558
80°	2652
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16746 cd/sqm



TEST NUMBER: P1258575  
 CATALOG NUMBER: P3AS24R559040D010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	333.7	12.1
10°-20°	954.1	34.5
20°-30°	1063.7	38.5
30°-40°	348.0	12.6
40°-50°	45.9	1.7
50°-60°	9.7	0.4
60°-70°	5.6	0.2
70°-80°	3.6	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2351.4	85.0
0°-40°	2699.4	97.6
0°-60°	2754.9	99.6
0°-90°	2765.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2765.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3497	
5°	3452	334
15°	3433	954
25°	2417	1064
35°	459	348
45°	54	46
55°	8	10
65°	6	6
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P1258575  
CATALOG NUMBER: P3AS24R559040D010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3497.3
2.5°	3472.3
5°	3451.6
7.5°	3501.4
10°	3549.2
12.5°	3524.3
15°	3432.9
17.5°	3287.4
20°	3079.6
22.5°	2792.8
25°	2416.7
27.5°	1938.8
30°	1402.7
32.5°	860.3
35°	459.2
37.5°	232.7
40°	122.6
42.5°	79.0
45°	54.0
47.5°	37.4
50°	20.8
52.5°	12.5
55°	8.3
57.5°	8.3
60°	8.3
62.5°	6.2
65°	6.2
67.5°	4.2
70°	4.2
72.5°	4.2
75°	4.2
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)