

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257938

Luminaire Tested: P3AS17R609040DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609040DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1457.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257938
CATALOG NUMBER: P3AS17R609040DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1257938

CATALOG NUMBER: P3AS17R609040DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73			73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59			59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344051
5°	340787
10°	330856
15°	309968
20°	274354
25°	229513
30°	179876
35°	130473
40°	86820
45°	54114
50°	29304
55°	8487
60°	7894
65°	7160
70°	7117
75°	7032
80°	6945
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54114 cd/sqm



TEST NUMBER: P1257938
 CATALOG NUMBER: P3AS17R609040DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.8	10.0
10°-20°	378.8	26.0
20°-30°	431.8	29.6
30°-40°	306.2	21.0
40°-50°	139.0	9.5
50°-60°	29.5	2.0
60°-70°	14.2	1.0
70°-80°	8.8	0.6
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	956.4	65.6
0°-40°	1262.6	86.7
0°-60°	1431.0	98.2
0°-90°	1457.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1457.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1569	
5°	1548	146
15°	1365	379
25°	949	432
35°	487	306
45°	174	139
55°	22	30
65°	14	14
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P1257938
CATALOG NUMBER: P3AS17R609040DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1569.0
2.5°	1563.4
5°	1548.2
7.5°	1521.9
10°	1485.9
12.5°	1434.6
15°	1365.4
17.5°	1278.2
20°	1175.7
22.5°	1064.9
25°	948.6
27.5°	829.5
30°	710.4
32.5°	596.8
35°	487.4
37.5°	390.5
40°	303.3
42.5°	229.9
45°	174.5
47.5°	130.2
50°	85.9
52.5°	40.2
55°	22.2
57.5°	19.4
60°	18.0
62.5°	16.6
65°	13.8
67.5°	12.5
70°	11.1
72.5°	9.7
75°	8.3
77.5°	6.9
80°	5.5
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)